

PropacPRO Complete Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICERINGER



FUNKTIONER

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Unshielded

Ventilation slots in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

SPECIFIKATIONER

| | |
|------------------------|-------------------------|
| Static Load: | 25kg |
| Product Type: | Case |
| Type: | Case for 19" Components |
| EMC Shielding: | No (Retrofittable) |
| Produktfamilie: | PropacPRO |

Table 1/3

| Katalognummer | Rack Height | Rack Width | Dybde | Pakke mængde | Usable Height | Usable Width |
|---------------|-------------|------------|-------|--------------|---------------|--------------|
| 24576-022 | 6U | 84HP | 446mm | 1 | 245.7mm | 432mm |
| 24576-005 | 3U | 42HP | 386mm | 1 | 112.3mm | 219mm |
| 24576-002 | 3U | 28HP | 326mm | 1 | 112.3mm | 148mm |
| 24576-010 | 3U | 84HP | 326mm | 1 | 112.3mm | 432mm |
| 24576-011 | 3U | 84HP | 386mm | 1 | 112.3mm | 432mm |
| 24576-021 | 6U | 84HP | 326mm | 1 | 245.7mm | 432mm |
| 24576-004 | 3U | 42HP | 326mm | 1 | 112.3mm | 219mm |
| 24576-006 | 3U | 63HP | 266mm | 1 | 112.3mm | 326mm |
| 24576-009 | 3U | 84HP | 266mm | 1 | 112.3mm | 432mm |
| 24576-012 | 3U | 84HP | 446mm | 1 | 112.3mm | 432mm |
| 24576-013 | 3U | 84HP | 506mm | 1 | 112.3mm | 432mm |
| 24576-003 | 3U | 42HP | 266mm | 1 | 112.3mm | 219mm |
| 24576-007 | 3U | 63HP | 326mm | 1 | 112.3mm | 326mm |
| 24576-001 | 3U | 28HP | 266mm | 1 | 112.3mm | 148mm |
| 24576-008 | 3U | 63HP | 386mm | 1 | 112.3mm | 326mm |

Table 2/3

| Katalognummer | Front Frame Construction | Cooling Option | Complies With | Finish | Højde | Materiale |
|---------------|--------------------------|----------------|-----------------|-----------------------------------|---------|-----------|
| 24576-022 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 289mm | Aluminium |
| 24576-005 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-002 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-010 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-011 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-021 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 289mm | Aluminium |

| Katalognummer | Front Frame Construction | Cooling Option | Complies With | Finish | Højde | Materiale |
|---------------|--------------------------|----------------|-----------------|-----------------------------------|---------|-----------|
| 24576-004 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-006 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-009 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-012 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-013 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-003 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-007 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-001 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |
| 24576-008 | Single Piece | No | IEC 60297-3-101 | Passivated, Struktur Pulvermaling | 155.5mm | Aluminium |

Table 3/3

| Katalognummer | Beskyttelsesgrad | Bredde |
|---------------|------------------|---------|
| 24576-022 | IP20 | 470.3mm |
| 24576-005 | IP20 | 257mm |
| 24576-002 | IP20 | 185.9mm |
| 24576-010 | IP20 | 470.3mm |
| 24576-011 | IP20 | 470.3mm |
| 24576-021 | IP20 | 470.3mm |
| 24576-004 | IP20 | 257mm |
| 24576-006 | IP20 | 363.7mm |
| 24576-009 | IP20 | 470.3mm |
| 24576-012 | IP20 | 470.3mm |
| 24576-013 | IP20 | 470.3mm |

| Katalognummer | Beskyttelsesgrad | Bredde |
|---------------|------------------|---------|
| 24576-003 | IP20 | 257mm |
| 24576-007 | IP20 | 363.7mm |
| 24576-001 | IP20 | 185.9mm |
| 24576-008 | IP20 | 363.7mm |

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE