


PropacPRO Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICERINGER



FUNKTIONER

Desktop case for individual assembly

Ventilation slots in base plate

Retrofitable EMC shielding

Prepared for GND/earthing

Conforms with DIN EN 62368-1

SPECIFIKATIONER

- Product Type:** Case
- Type:** Case for Individual Electronic Components
- Produktfamilie:** PropacPRO

Table 1/2

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
14576-465	6U	84HP	386mm	1	262.8mm	432mm
14576-241	4U	63HP	266mm	1	174mm	326mm

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
14576-169	3U	84HP	506mm	1	130mm	432mm
14576-463	6U	84HP	326mm	1	262.8mm	432mm
14576-467	6U	84HP	446mm	1	262.8mm	432mm
14576-143	3U	63HP	326mm	1	130mm	326mm
14576-123	3U	42HP	326mm	1	130mm	219mm
14576-043	2U	63HP	326mm	1	85.1mm	326mm
14576-167	3U	84HP	446mm	1	130mm	432mm
14576-023	2U	42HP	326mm	1	85.1mm	219mm
14576-125	3U	42HP	386mm	1	130mm	219mm
14576-243	4U	63HP	326mm	1	174mm	326mm
14576-223	4U	42HP	326mm	1	174mm	219mm
14576-121	3U	42HP	266mm	1	130mm	219mm
14576-145	3U	63HP	386mm	1	130mm	326mm
14576-269	4U	84HP	506mm	1	174mm	432mm
14576-041	2U	63HP	266mm	1	85.1mm	326mm
14576-245	4U	63HP	386mm	1	174mm	326mm
14576-165	3U	84HP	386mm	1	130mm	432mm
14576-045	2U	63HP	386mm	1	85.1mm	326mm

Table 2/2

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
14576-469	6U	84HP	506mm	1	262.8mm	432mm
14576-247	4U	63HP	446mm	1	174mm	326mm
14576-103	3U	28HP	326mm	1	130mm	148mm
14576-221	4U	42HP	266mm	1	174mm	219mm
14576-267	4U	84HP	446mm	1	174mm	432mm
14576-141	3U	63HP	266mm	1	130mm	326mm
14576-161	3U	84HP	266mm	1	130mm	432mm
14576-163	3U	84HP	326mm	1	130mm	432mm
14576-021	2U	42HP	266mm	1	85.1mm	219mm
14576-265	4U	84HP	386mm	1	174mm	432mm
14576-101	3U	28HP	266mm	1	130mm	148mm

Table 1/2

Katalognummer	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Højde
14576-465	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	289mm
14576-241	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-169	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-463	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	289mm
14576-467	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	289mm
14576-143	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-123	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-043	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	111mm
14576-167	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-023	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	111mm
14576-125	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-243	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-223	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-121	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm

Katalognummer	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Højde
14576-145	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-269	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-041	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	111mm
14576-245	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-165	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-045	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	111mm

Table 2/2

Katalognummer	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Højde
14576-469	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	289mm
14576-247	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-103	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-221	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-267	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-141	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-161	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm

Katalognummer	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Højde
14576-163	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14576-021	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	111mm
14576-265	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14576-101	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm

Table 1/2

Katalognummer	Materiale	Beskyttelsesgrad	Static Load	Bredde
14576-465	Aluminium	IP20	25kg	470.3mm
14576-241	Aluminium	IP20	25kg	363.7mm
14576-169	Aluminium	IP20	25kg	470.3mm
14576-463	Aluminium	IP20	25kg	470.3mm
14576-467	Aluminium	IP20	25kg	470.3mm
14576-143	Aluminium	IP20	25kg	363.7mm
14576-123	Aluminium	IP20	25kg	257mm
14576-043	Aluminium	IP20	25kg	363.7mm
14576-167	Aluminium	IP20	25kg	470.3mm
14576-023	Aluminium	IP20	25kg	257mm
14576-125	Aluminium	IP20	25kg	257mm
14576-243	Aluminium	IP20	25kg	363.7mm
14576-223	Aluminium	IP20	25kg	257mm
14576-121	Aluminium	IP20	25kg	257mm
14576-145	Aluminium	IP20	25kg	363.7mm
14576-269	Aluminium	IP20	25kg	470.3mm
14576-041	Aluminium	IP20	25kg	363.7mm
14576-245	Aluminium	IP20	25kg	363.7mm
14576-165	Aluminium	IP20	25kg	470.3mm
14576-045	Aluminium	IP20	25kg	363.7mm

Table 2/2

Katalognummer	Materiale	Beskyttelsesgrad	Static Load	Bredde
---------------	-----------	------------------	-------------	--------

14576-469	Aluminium	IP20	25kg	470.3mm
14576-247	Aluminium	IP20	25kg	363.7mm
14576-103	Aluminium	IP20	25kg	185.9mm
14576-221	Aluminium	IP20	25kg	257mm
14576-267	Aluminium	IP20	25kg	470.3mm
14576-141	Aluminium	IP20	25kg	363.7mm
14576-161	Aluminium	IP20	25kg	470.3mm
14576-163	Aluminium	IP20	25kg	470.3mm
14576-021	Aluminium	IP20	25kg	257mm
14576-265	Aluminium	IP20	25kg	470.3mm
14576-101	Aluminium	IP20	25kg	185.9mm

YDERLIGERE PRODUKTOPLYSNINGER

Case, 2 U with side panel for tip-up carrying handle on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE