

PropacPRO Front Hood



The front hood bottom hinged can be assembled on to a PropacPRO case. It protects the PCB from accidental operations. A retrofittable lock can be installed.

CERTIFICERINGER



FUNKTIONER

Mounting of hinges at top or bottom

Lock (max. 2) retrofittable

From acrylic glass, hinged, removable

Lateral cover (item 5) also serves as vertical EMC shielding of side panels

SPECIFIKATIONER

Rack Height:	3U
Works With:	Cases
Product Type:	Cover Plate
Type:	Front Hood
Produktfamilie:	PropacPRO
Materiale:	Thermoplastic

Table 1/1

Katalognummer	Rack Width	Pakke mængde	Dybde
24576-080	28HP	1	
24576-083	84HP	1	175mm
24576-082	63HP	1	

Katalognummer	Rack Width	Pakke mængde	Dybde
24576-081	42HP	1	

YDERLIGERE PRODUKTOPLYSNINGER

Cannot be combined with design elements.

Other heights available on request.

Before assembly of hood feet must be fixed to case; please order separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE