

PSU 19" AC/DC Linear Regulator, Single

Linear regulator for applications requiring very low output noise level.



CERTIFICERINGER



FUNKTIONER

1 output voltage

High control accuracy, low residual ripple and low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

SPECIFIKATIONER

Table 1/2

| Katalognummer | Type | Indgangsspænding AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|---------------|----------------------|---------------------|-------|---------------------------|-----------|-----------|
| 13105-004 | 19" Linear Regulator | 230V | 16W | 1 | 24V | 0.6A |
| 13105-003 | 19" Linear Regulator | 230V | 15W | 1 | 15V | 1A |
| 13105-009 | 19" Linear Regulator | 230V | 36W | 1 | 24V | 1.5A |

| Katalognummer | Type | Indgangsspænding AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|---------------|----------------------|---------------------|-------|---------------------------|-----------|-----------|
| 13105-001 | 19" Linear Regulator | 230V | 8W | 1 | 5V | 1.5A |
| 13105-011 | 19" Linear Regulator | 230V | 30W | 1 | 5V | 6A |
| 13105-008 | 19" Linear Regulator | 230V | 33W | 1 | 15V | 2.2A |
| 13105-007 | 19" Linear Regulator | 230V | 31W | 1 | 12V | 2.8A |
| 13105-012 | 19" Linear Regulator | 230V | 50W | 1 | 12V | 4.2A |
| 13105-014 | 19" Linear Regulator | 230V | 60W | 1 | 24V | 2.5A |
| 13105-006 | 19" Linear Regulator | 230V | 20W | 1 | 5V | 4A |
| 13105-002 | 19" Linear Regulator | 230V | 13W | 1 | 12V | 1.1A |
| 13105-013 | 19" Linear Regulator | 230V | 53W | 1 | 15V | 3.5A |

Table 2/2

| Katalognummer | Rack Height | Rack Width | Dybde | Pakke mængde | Certificeringer |
|---------------|-------------|------------|----------|--------------|----------------------|
| 13105-004 | 3U | 6HP | 171.93mm | 1 | RoHS, CE, EN 62368-1 |
| 13105-003 | 3U | 6HP | 171.93mm | 1 | CE, EN 62368-1, RoHS |
| 13105-009 | 3U | 10HP | 171.93mm | 1 | CE, RoHS |
| 13105-001 | 3U | 6HP | 171.93mm | 1 | EN 62368-1, CE, RoHS |
| 13105-011 | 3U | 14HP | 171.93mm | 1 | CE, RoHS |
| 13105-008 | 3U | 10HP | 171.93mm | 1 | CE, RoHS |
| 13105-007 | 3U | 10HP | 171.93mm | 1 | CE, RoHS |
| 13105-012 | 3U | 14HP | 171.93mm | 1 | CE, RoHS |
| 13105-014 | 3U | 14HP | 171.93mm | 1 | RoHS, CE |
| 13105-006 | 3U | 10HP | 171.93mm | 1 | CE, RoHS |
| 13105-002 | 3U | 6HP | 171.93mm | 1 | CE, EN 62368-1, RoHS |
| 13105-013 | 3U | 14HP | 171.93mm | 1 | RoHS, CE |

YDERLIGERE PRODUKTOPLYSNINGER

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelser af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE