

Tray Handle

The tray handle can be clip into a cutout in the side panel of a case. 2 sizes available.



CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity 30 kg/pair

Side panel thickness min. 1,0 mm

SPECIFIKATIONER

Static Load:	30kg
Farve:	Black
Works With:	Cases
Produktfamilie:	RatiopacPRO; RatiopacPRO AIR; PropacPRO; CompacPRO; Comptec
Product Type:	Handle
Materiale:	Polycarbonate
Type:	Static

Table 1/1

Katalognummer	Højde	Bredde	Dybde	Pakke mængde	Håndtagstype	Flammability Rating
60225-012	79mm	187mm	22mm	1	Tray Handle	UL® 94V-0
60229-004	56mm	110mm	18mm	1	Tray Handle	UL® 94V-0

YDERLIGERE PRODUKTOPLYSNINGER

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE