

## Varistar 19" Panel/Slide Mount



Slide mounts with adjustable increments.

### CERTIFICERINGER

---



### FUNKTIONER

---

Depth-adjustable in 25 mm increments

In accordance with IEC 60297-1 (DIN 41 494, Part 1)

Assembly in 600 mm wide cabinets directly on the frame

For 800 mm width adapter bracket for reduced width is necessary, for partial-height mounting depth members are necessary

Dimensions are engraved in U increments (1 ... 52 U)

Made of Steel, 2 mm thick

Subsequent assembly possible

## SPECIFIKATIONER

**Product Type:** Slide Mount

**Materiale:** Stål

Table 1/2

Katalognummer	Rack Height	Højde	Finish	Pakke mængde	Farve	Farvekode
23130-036	47U	2200mm	Aluminum-Zinc Plated	2		
23130-013	33U	1600mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-039	16U	750mm	Aluminum-Zinc Plated	2		
23130-029	16U	750mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-588	52U	2450mm	Aluminum-Zinc Plated	2	Black Grey	RAL 7021
23130-023	33U	1600mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-033	33U	1600mm	Aluminum-Zinc Plated	2		
23130-014	38U	1800mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-037	8U	400mm	Aluminum-Zinc Plated	2		
23130-022	29U	1400mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-015	42U	2000mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-030	20U	900mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-035	42U	2000mm	Aluminum-Zinc Plated	2		
23130-021	24U	1200mm	Struktur Pulvermaling	2	Light Grey	RAL 7035

Katalognummer	Rack Height	Højde	Finish	Pakke mængde	Farve	Farvekode
23130-040	20U	900mm	Aluminum-Zinc Plated	2		
23130-020	20U	900mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-032	29U	1400mm	Aluminum-Zinc Plated	2		
23130-016	47U	2200mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-019	16U	750mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-018	12U	550mm	Struktur Pulvermaling	2	Black Grey	RAL 7021

Table 2/2

Katalognummer	Rack Height	Højde	Finish	Pakke mængde	Farve	Farvekode
23130-017	8U	400mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-031	24U	1200mm	Aluminum-Zinc Plated	2		
23130-570	52U	2450mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-026	47U	2200mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-027	8U	400mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-011	24U	1200mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-038	12U	550mm	Aluminum-Zinc Plated	2		
23130-034	38U	1800mm	Aluminum-Zinc Plated	2		
23130-024	38U	1800mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-028	12U	550mm	Struktur Pulvermaling	2	Light Grey	RAL 7035
23130-012	29U	1400mm	Struktur Pulvermaling	2	Black Grey	RAL 7021
23130-025	42U	2000mm	Struktur Pulvermaling	2	Light Grey	RAL 7035

Table 1/2

Katalognummer	Length	Pakkeenhed
23130-036	2095mm	Pair
23130-013	1495mm	
23130-039	745mm	
23130-029	745mm	
23130-588	2345mm	
23130-023	1495mm	
23130-033	1495mm	
23130-014	1695mm	Pair
23130-037	395mm	
23130-022	1295mm	
23130-015	1895mm	Pair
23130-030	895mm	
23130-035	1895mm	Pair
23130-021	1095mm	
23130-040	895mm	
23130-020	895mm	
23130-032	1295mm	Pair
23130-016	2095mm	Pair
23130-019	745mm	
23130-018	545mm	

Table 2/2

Katalognummer	Length	Pakkeenhed
23130-017	395mm	
23130-031	1095mm	Pair
23130-570	2345mm	
23130-026	2095mm	
23130-027	395mm	
23130-011	1095mm	Pair
23130-038	545mm	
23130-034	1695mm	Pair
23130-024	1695mm	
23130-028	545mm	
23130-012	1295mm	Pair
23130-025	1895mm	

## YDERLIGERE PRODUKTOPLYSNINGER

---

For 19" partial-height mounting depth members are necessary.

Metric panel/slide mounts available on request.

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**