

# Varistar CP Base Plate With Cable Entry

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.



## FUNKTIONER

Installation from outside

Cutout at rear

60 mm deep

Cable ducting with IP 55 / EMC gasket

## SPECIFIKATIONER

**Product Type:** Cabinet/Rack Base

**Materiale:** Stål

Table 1/2

Katalognummer	Bredde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve	Farvekode
21630-645	600mm	1000mm		1		
21630-649	800mm	800mm		1		
21630-835	800mm	1000mm		1		
21630-829	600mm	1000mm	IP20	1		
21630-831	600mm	1200mm	IP20	1		
21630-644	600mm	900mm		1		
21630-826	600mm	600mm	IP20	1		
21630-834	800mm	900mm	IP20	1		
21630-701	600mm	900mm		1	Black Grey	RAL 7021

Katalognummer	Bredde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve	Farvekode
21630-646	600mm	1100mm		1		
21630-653	800mm	1200mm		1		
21630-700	600mm	800mm		1	Black Grey	RAL 7021
21630-833	800mm	800mm	IP20	1		
21630-827	600mm	800mm	IP20	1		
21630-650	800mm	900mm		1		
21630-699	600mm	600mm		1	Black Grey	RAL 7021
21630-698	600mm	300mm		1	Black Grey	RAL 7021
21630-832	800mm	600mm	IP20	1		
21630-828	600mm	900mm	IP20	1		
21630-651	800mm	1000mm		1		

Table 2/2

Katalognummer	Bredde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve	Farvekode
21630-710	800mm	1200mm		1	Black Grey	RAL 7021
21630-652	800mm	1100mm		1		
21630-642	600mm	600mm		1		
21630-707	800mm	900mm		1	Black Grey	RAL 7021
21630-837	800mm	1200mm	IP20	1		
21630-708	800mm	1000mm		1	Black Grey	RAL 7021
21630-830	600mm	1100mm	IP20	1		
21630-706	800mm	800mm		1	Black Grey	RAL 7021
21630-643	600mm	800mm		1		
21630-705	800mm	600mm		1	Black Grey	RAL 7021
21630-836	800mm	1100mm	IP20	1		
21630-709	800mm	1100mm		1	Black Grey	RAL 7021
21630-704	600mm	1200mm		1	Black Grey	RAL 7021
21630-648	800mm	600mm		1		
21630-703	600mm	1100mm		1	Black Grey	RAL 7021
21630-647	600mm	1200mm		1		
21630-702	600mm	1000mm		1	Black Grey	RAL 7021

Table 1/2

Katalognummer	Complies With	Finish	Works With
---------------	---------------	--------	------------

21630-645		Hot-Dip Galvanized	
21630-649		Hot-Dip Galvanized	
21630-835	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-829	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-831	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-644		Hot-Dip Galvanized	
21630-826	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-834	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-701			
21630-646		Hot-Dip Galvanized	
21630-653		Hot-Dip Galvanized	
21630-700			
21630-833	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-827	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-650		Hot-Dip Galvanized	
21630-699			
21630-698			
21630-832	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-828	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-651		Hot-Dip Galvanized	

Table 2/2

Katalognummer	Complies With	Finish	Works With
21630-710			
21630-652		Hot-Dip Galvanized	
21630-642		Hot-Dip Galvanized	
21630-707			
21630-837	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-708			
21630-830	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-706			
21630-643		Hot-Dip Galvanized	
21630-705			
21630-836	IEC 61587-1, IEC 61587-3	Hot-Dip Galvanized	Varistar CP
21630-709			
21630-704			

Katalognummer	Complies With	Finish	Works With
21630-648		Hot-Dip Galvanized	
21630-703			
21630-647		Hot-Dip Galvanized	
21630-702			

## YDERLIGERE PRODUKTOPLYSNINGER

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

Please purchase the grounding kit separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**