

Varistar CP Base/Plinth Side

Sides trim to mount to Varistar CP base/plinth



FUNKTIONER

Base/plinth sides, plain

SPECIFIKATIONER

Product Type: Cabinet/Rack Base

Materiale: Stål

Table 1/2

Katalognummer	Højde	Dybde	Pakke mængde	Farve	Farvekode	Finish
24630-077	100mm	600mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-083	100mm	300mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-043	200mm	1200mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-078	100mm	800mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-040	100mm	1200mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-080	200mm	600mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-042	200mm	1100mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-081	200mm	800mm	1	Black Grey	RAL 7021	Struktur Pulvermaling

Katalognummer	Højde	Dybde	Pakke mængde	Farve	Farvekode	Finish
24630-038	100mm	1000mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-079	100mm	900mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-084	200mm	300mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-039	100mm	1100mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-082	200mm	900mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
24630-041	200mm	1000mm	1	Black Grey	RAL 7021	Struktur Pulvermaling

Table 2/2

Katalognummer	Type	Pakkeenhed
24630-077	Plinth Side	Pair
24630-083	Plinth Side	
24630-043	Plinth Side	Pair
24630-078	Plinth Side	Pair
24630-040	Plinth Side	Pair
24630-080	Plinth Side	Pair
24630-042	Plinth Side	Pair
24630-081	Plinth Side	Pair
24630-038	Plinth Side	Pair
24630-079	Plinth Side	Pair
24630-084	Plinth Side	
24630-039	Plinth Side	Pair
24630-082	Plinth Side	Pair
24630-041	Plinth Side	Pair

YDERLIGERE PRODUKTOPLYSNINGER

Please order base/plinth for front/rear separately.

Cannot be used in conjunction with castors

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE