

Varistar CP Base/Plinth

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



FUNKTIONER

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

SPECIFIKATIONER

Product Type: Cabinet/Rack Base

Materiale: Stål

Table 1/2

Katalognummer	Højde	Bredde	Pakke mængde	Farve	Farvekode	Dybde
24630-034	100mm	600mm	1	Black Grey	RAL 7021	600mm
24630-037	200mm	800mm	1	Black Grey	RAL 7021	
24630-067	200mm	800mm	1	Black Grey	RAL 7021	
24630-066	200mm	600mm	1	Black Grey	RAL 7021	
24630-036	200mm	600mm	1	Black Grey	RAL 7021	
24630-064	100mm	600mm	1	Black Grey	RAL 7021	
24630-065	100mm	800mm	1	Black Grey	RAL 7021	
24630-035	100mm	800mm	1	Black Grey	RAL 7021	

Table 2/2

Katalognummer	Finish	Type
24630-034	Struktur Pulvermaling	Base Plinth, Perforated
24630-037	Struktur Pulvermaling	Base Plinth, Perforated

Katalognummer	Finish	Type
24630-067	Struktur Pulvermaling	Base Plinth, Plain
24630-066	Struktur Pulvermaling	Base Plinth, Plain
24630-036	Struktur Pulvermaling	Base Plinth, Perforated
24630-064	Struktur Pulvermaling	Base Plinth, Plain
24630-065	Struktur Pulvermaling	Base Plinth, Plain
24630-035	Struktur Pulvermaling	Base Plinth, Perforated

YDERLIGERE PRODUKTOPLYSNINGER

Please order side trims separately.

Cannot be used in conjunction with castors

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE