We connect and protect

# VMEbus J2 Backplane



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

## CERTIFICERINGER

RoHS COMPLIANT

VITA Open Standards, Open Markets

## FUNKTIONER

In accordance with ANSI/VITA 1-1994 VME64 standard

3 U with J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination passive

Supply voltages can be provided via powerbugs (ring tag M4) or FASTONs

Multiple backplanes can be placed side by side without loss of slot space

## SPECIFIKATIONER

Table 1/2

| Katalognummer | Product Type | Number of Slots | Rack Height | Backplane Type | System Slot | Slot Width |
|---|---|---|---|---|---|---|
| 23001-051 | Backplane | 21 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |
| 23001-046 | Backplane | 16 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |
| 23001-040 | Backplane | 10 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |
| 23001-036 | Backplane | 6 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |
| 23001-035 | Backplane | 5 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |

| Katalognummer | Product Type | Number of Slots | Rack Height | Backplane Type | System Slot | Slot Width |
|---|---|---|---|---|---|---|
| 23001-034 | Backplane | 4 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |
| 23001-033 | Backplane | 3 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |
| 23001-032 | Backplane | 2 | 3U | VMEbus, J2 | Slot 1 Left | 4HP |

Table 2/2

| Katalognummer | Connector Type | Power Connector Type | Højde | Bredde | Pakke mængde |
|---|---|---|---|---|---|
| 23001-051 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 425.3mm | 1 |
| 23001-046 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 321.3mm | 1 |
| 23001-040 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 199.2mm | 1 |
| 23001-036 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 120.5mm | 1 |
| 23001-035 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 100.2mm | 1 |
| 23001-034 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 79.8mm | 1 |
| 23001-033 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 59.7mm | 1 |
| 23001-032 | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | 128.5mm | 40.4mm | 1 |

## YDERLIGERE PRODUKTOPLYSNINGER

Other configurations available on request.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

**North America**
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

**Europe**
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

**Asia**
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

**Middle East & India**
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.