

# Dry Contact Cable

## Data Solutions



Dry Contact Cable to connect I/O sensors e.g. smoke for Enlogic.

### FEATURES

Dry Contact Cable to connect I/O sensors e.g. smoke

1 m Cable to Sensor box with integrated magnet for easy mounting and 1.8 m connection Cable

For Enlogic

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

### SPECIFICATIONS

Table 1/1

Catalog Number	Works With	Height	Package Quantity	Plug Type	Removable Input Cable
EA9110	RackPower	260mm	1	RJ45	No

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**