

# Threaded Bridle Ring



## CERTIFICATIONS



## FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/2

Catalog Number	Article Number	Diameter	Screw Diameter	Screw Type	Screw Length	Ultimate Static Load
4BRT20		31.8 mm	6	Metal	19mm	220N
4BRT32		50 mm	6	Metal	19mm	220N
4BRT64		100 mm	6	Metal	19mm	220N
2BRT8		12.7 mm	4.8	Metal	14.3mm	220N
2BRT20		31.8 mm	4.8	Metal	14.3mm	220N
2BRT32		50.8 mm	4.8	Metal	14.3mm	220N
2BRT12		19.1 mm	4.8	Metal	14.3mm	220N

Catalog Number	Article Number	Diameter	Screw Diameter	Screw Type	Screw Length	Ultimate Static Load
4BRT20WS		31.8 mm	14	Wood	19.1mm	220N
4BRT32WS	172923	50 mm	14	Wood	19mm	220N

Table 2/2

Catalog Number	Article Number	Certifications
4BRT20		cUL, UL
4BRT32		UL, cUL
4BRT64		cUL, UL
2BRT8		cUL, UL
2BRT20		cUL, UL
2BRT32		UL, cUL
2BRT12		cUL, UL
4BRT20WS		UL, cUL
4BRT32WS	172923	UL, ITB, cUL

## ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

