

Socket Strip, SCHUKO, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Installation height 1 U

Output via SCHUKO sockets

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal or vertical mounting

In accordance with DIN 57620

SPECIFICATIONS

- Length:** 438.5mm
- Material:** Aluminum; Polyamide
- Product Type:** Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-354	SCHUKO	6	No	230V	Overcurrent Protection	1

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-353	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-343	SCHUKO	8	No	230V		1
60110-352	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-345	SCHUKO	8	No	230V		1
60110-344	SCHUKO	8	No	230V		1

Table 2/2

Catalog Number	Color	Depth	Finish
60110-354	Red	44mm	Anodized
60110-353	Black	44mm	Anodized
60110-343	Grey	44mm	Anodized
60110-352	Grey	44mm	Anodized
60110-345	Red	44mm	Anodized
60110-344	Black	44mm	Anodized

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE