

Outdoor Comline FTTX Cabinet With Dual Access, 600H 800W 600D

Data Solutions

CATALOG NUMBER

12349-007



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

CERTIFICATIONS



FEATURES

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

PRODUCT ATTRIBUTES

Product Type: Outdoor Cabinet

Product Family: Comline FTTX

Rack Height: 12U

Height: 600mm

Width: 800mm

Depth: 600mm

Wall Type: Single Walled

Door Type: Single Door

Access: Front; Back

Cooling: Insulation

EMC Shielding: No

Complies With: IEC 61969-1; IEC 61969-2; IEC 60917-1; IEC 60917-2; ETS 300119; IEC 60529; DIN EN 50178; VDE 0160

Package Quantity: 1

Finish: Powder Coated

Material: Aluminum

Net Weight: 70kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE