

Threaded Bridle Ring



FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Article Number	Diameter	Screw Diameter	Screw Type	Screw Length	Ultimate Static Load
PTB6	172921	12 mm	6	Metal	32mm	220N
PTB8	172922	16 mm	8	Metal	32mm	220N
GR50	172920	50 mm	6	Metal	18mm	220N

ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

