

Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 95 mm² Ropelay, Right Hand

Data Solutions

CATALOG NUMBER

PBWT20X5RH



FEATURES

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

PRODUCT ATTRIBUTES

Material: Graphite; Steel; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 95 mm² Ropelay

Conductor Outer Diameter, Nominal: 15.52mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBWX5RH

Welding Material: PB150, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S02F, Sold Separately

Hammer Die: WD83, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE