


Labrack Slide Rail, 40 kg, 1 Pair

CATALOG NUMBER

20119-080



Labrack Slide Rail with 40 kg load capacity for mounting on the bare cabinet uprights or 19" panel/slide mounts. The slide rail supports shelf of heavy 19" Chassis.

CERTIFICATIONS



FEATURES

For assembly on mobile 19" lab racks; with panel mounts also on stationary 19" lab racks

Static load-carrying capacity 40 kg per pair

PRODUCT ATTRIBUTES

Package Quantity: 2

Finish: Zinc Plated

Material: Steel

Product Family: Labrack

Product Type: Slide Rail

Static Load: 40kg

Net Weight: 0.99kg

ADDITIONAL PRODUCT DETAILS

Mounting angles are necessary for assembly on stationary 19" lab rack, please order them separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE