

Double Test Socket, Ø 2 mm



Double test sockets for mounting plane 1 and 2, short and long type.

Solder temperature should only be applied for a maximum of 5 seconds. The plastic body should be protected from the solder wave when wave soldering.

CERTIFICATIONS



FEATURES

Double test sockets for Front Element System

SPECIFICATIONS

Diameter: 2mm
Product Type: Socket

Table 1/2

| Catalog Number | Type | Package Quantity | Voltage AC | Max Current | Test Voltage @ 50 Hz | Ambient Temperature |
|----------------|-------------------------|------------------|------------|-------------|----------------------|---------------------|
| 69004-089 | Long, Mounting Plane 1 | 1 | 30V | 1A | 1kV | -25 to 70°C |
| 69004-131 | Short, Mounting Plane 1 | 1 | 30V | 1A | 1kV | -25 to 70°C |
| 69004-090 | Long, Mounting Plane 2 | 10 | 30V | 1A | 1kV | -25 to 70°C |

Table 2/2

| Catalog Number | Solder Temperature | Flammability Rating |
|----------------|--------------------|---------------------|
| 69004-089 | 260°C | UL® 94V-0 |

| Catalog Number | Solder Temperature | Flammability Rating |
|----------------|--------------------|---------------------|
| 69004-131 | 260°C | UL® 94V-0 |
| 69004-090 | 260°C | UL® 94V-0 |

ADDITIONAL PRODUCT DETAILS

Dimensions of connecting pins: 0.3 × 0.6 mm.

Required front panel drill hole: Ø 4 mm.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE