

Plug-In Unit Front Panel for Static Trapezoid Handle



The front panel enables the assembly of a plastic or Alu-profile static trapezoid handle. The front panel cannot be shielded with a textile gasket.

CERTIFICATIONS



FEATURES

Front panel, unshielded

Front panel, Al, 2.5 mm, front anodized, conductive

SPECIFICATIONS

| | |
|------------------------|------------------------------|
| Depth (D): | 2.5mm |
| Material: | Aluminum |
| Finish: | Anodized; Passivated |
| Accessory Type: | Front panel |
| Product Type: | Front Panel |
| Type: | Front Panel for Handle (PIU) |

Table 1/2

| Catalog Number | Rack Height | Rack Width | Package Quantity | Handle Type | Mounting | Front Finish |
|----------------|-------------|------------|------------------|-------------|----------|--------------|
|----------------|-------------|------------|------------------|-------------|----------|--------------|

| | | | | | | |
|-----------|----|------|---|--|----------------|----------|
| 30847-605 | 3U | 6HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-604 | 3U | 5HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-626 | 6U | 4HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-627 | 6U | 5HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-625 | 6U | 3HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-628 | 6U | 6HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-609 | 3U | 12HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-629 | 6U | 7HP | 1 | Trapezoid, Static | Screw-on Front | Anodized |
| 30847-603 | 3U | 4HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-608 | 3U | 10HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-630 | 6U | 8HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-607 | 3U | 8HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |

| | | | | | | |
|-----------|----|------|---|--|----------------|----------|
| 30847-602 | 3U | 3HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-631 | 6U | 10HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |
| 30847-632 | 6U | 12HP | 1 | Trapezoid, Static | Screw-on Front | Anodized |
| 30847-606 | 3U | 7HP | 1 | Trapezoid, Static, Aluminum Profile | Screw-on Front | Anodized |

Table 2/2

| Catalog Number | Rear Finish | Treated Edges | Complies With | EMC Shielding | Height (H) | Width (W) |
|----------------|-------------|---------------|-----------------|---------------|------------|-----------|
| 30847-605 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 30.1mm |
| 30847-604 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 25mm |
| 30847-626 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 20mm |
| 30847-627 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 25mm |
| 30847-625 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 14.9mm |
| 30847-628 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 30.1mm |
| 30847-609 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 60.6mm |
| 30847-629 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 35.2mm |
| 30847-603 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 20mm |
| 30847-608 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 50.5mm |
| 30847-630 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 40.3mm |
| 30847-607 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 40.3mm |
| 30847-602 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 14.9mm |

| Catalog Number | Rear Finish | Treated Edges | Complies With | EMC Shielding | Height (H) | Width (W) |
|----------------|-------------|---------------|-----------------|---------------|------------|-----------|
| 30847-631 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 50.5mm |
| 30847-632 | Conductive | No | IEC 60297-3-101 | No | 261.8mm | 60.6mm |
| 30847-606 | Conductive | No | IEC 60297-3-101 | No | 128.4mm | 35.2mm |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE