

# Comptec GND/Earthing Kit



Protective GND/earthing connections in accordance with:  
 DIN EN 50178, VDE 0160 DIN EN 62368-1, VDE 0805 DIN EN  
 61010-1, VDE 0411 Part 1 DIN EN 61010-1A2, VDE 0411  
 Part 1/A1.

## CERTIFICATIONS



## FEATURES

Protective GND/earthing connections in accordance with: DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805  
 DIN EN 61010-1 /VDE 0411 Part 1 DIN EN 61010-1A2 /VDE 0411 Part 1/A1

VDE tested

## SPECIFICATIONS

- Product Family:** Comptec
- Type:** Grounding Kit
- Product Type:** Grounding Kit

Table 1/1

Catalog Number	Package Quantity	Works With
21100-490	1	Cases, Steel Cover
21100-448	1	Cases, Steel Cover
21100-347	1	Cases, Aluminum Cover

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**