

# nVent CADDY Cat CM Double J-Hook, 70 Cable Capacity, Cat 5e, 30 Cable Capacity, Cat 6A

## Data Solutions

### CATALOG NUMBER

**CAT100CM**



### CERTIFICATIONS



### FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

System offers a convenient pathway for wires and cables

Double J-Hooks can be mounted vertically along the same drop rod to create a tree configuration

Allows addition of cables even when fixed flush to overhead decking

Specially designed double J-Hook has large-diameter, rounded support surfaces

Rounded edges help prevent over-bending and kinking of cables

Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure

Compliant with NEC® and ANSI®/TIA structured cabling systems standards


PRODUCT ATTRIBUTES

|                            |
|----------------------------|
| Article Number: 181976     |
| Material: Steel            |
| Finish: Electrogalvanized  |
| Cable Capacity, Cat 5e: 70 |
| Cable Capacity, Cat 6: 50  |
| Cable Capacity, Cat 6A: 30 |
| A: 185mm                   |
| Area: 80.2mm²              |
| Hole Size (HS): 9.5mm      |

ADDITIONAL PRODUCT DETAILS

Area shown is the combined value for both sides. Divide by 2 for area of each side.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE