

# nVent CADDY Cat 425 Adjustable Cable Support with Flange Clip, 100 mm, 150 mm dia, 3.2–6.4 mm Flange

## Data Solutions

### CATALOG NUMBER

---

**CAT42524SM**



### CERTIFICATIONS

---



### FEATURES

---

Requires only a hammer to install

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Simple unlocking and locking of bar allows for additional cables to be added easily after installation

Adjustable strap allows for multiple support sizes to reduce inventory

Cost effective alternative to expensive cable tray


cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems

Suitable for air handling spaces (plenum)

PRODUCT ATTRIBUTES

|                                               |
|-----------------------------------------------|
| Article Number: 181620                        |
| Material: Steel; Polyethylene; Spring Steel   |
| Finish: nVent CADDY Armour; Electrogalvanized |
| Diameter (Ø): 100mm; 150mm                    |
| Area: 13181mm²                                |
| Cable Capacity, Cat 5e: 425                   |
| Cable Capacity, Cat 6: 325                    |
| Cable Capacity, Cat 6A: 210                   |
| Flange Thickness (FT): 3.2 – 6.4mm            |
| Static Load: 450N                             |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**