

Single-Sided Shelf

Data Solutions



The Single-Sided Shelf mounts to 19-inch rack angles to house voice/data networking equipment. Please note the load rating is 75 lb. (34 kg).

FEATURES

The Single-Sided Shelf mounts to 19-inch rack angles to house voice/data networking equipment

Please note the load rating is 75 lb. (34 kg)

SPECIFICATIONS

Color Code: RAL 9005

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Thickness	Rack Units
ESH1915V	17367	Mild Steel	Powder Coated	Jet Black	1.52mm	2U
ESH198	35209	Mild Steel	Powder Coated	Jet Black	1.52mm	2U
ESH1915	17366	Mild Steel	Powder Coated	Jet Black	1.52mm	2U
ESH1917	35219	Mild Steel	Powder Coated	Jet Black	1.52mm	2U

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Type
ESH1915V	17367	95mm	482mm	381mm	Vented
ESH198	35209	95mm	482mm	203mm	Solid
ESH1915	17366	95mm	482mm	381mm	Solid

Catalog Number	Article Number	Height	Width	Depth	Type
ESH1917	35219	95mm	482mm	432mm	Solid

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE