

APO Base



APO enclosures are designed for use as insulated electrical junction boxes, terminal wiring boxes, instrument housings and electrical control enclosures in highly corrosive environments.

FEATURES

Bases are maintenance free and corrosion resistant

All bases can be easily modified to customer specifications

Brass M4 threaded inserts are factory installed for mounting plate attachment

7 to 6 bosses suitable for M6 threaded inserts are molded into the base (dependant on enclosure size).

Maintain UL / CSA Type 4x with up to 5 extension collars

SPECIFICATIONS

Material: Fiberglass
Color: Light Gray
Color Code: RAL 7035
Finish: Smooth Matte

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth |
|----------------|----------------|--------|-------|-------|
| A1-BASELG | A1-BASELG | 186mm | 151mm | 95mm |
| A31-BASELG | A31-BASELG | 302mm | 186mm | 131mm |
| A41-BASELG | A41-BASELG | 302mm | 302mm | 131mm |
| A51-BASELG | A51-BASELG | 488mm | 302mm | 131mm |
| A12-BASELG | A12-BASELG | 603mm | 603mm | 131mm |
| A81-BASELG | A81-BASELG | 558mm | 302mm | 131mm |
| A61-BASELG | A61-BASELG | 603mm | 302mm | 131mm |
| A11-BASELG | A11-BASELG | 603mm | 372mm | 131mm |
| A71-BASELG | A71-BASELG | 372mm | 302mm | 131mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE