

ProLine G2 Solid Top

ProLine G2 Solid tops are used to close the top opening on an enclosure frame.



FEATURES

Lifting eyes can be used to attach the solid top, in place of the included hardware

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Additional support provisions need to be made to support top mount air conditioners or other top mount accessories

Includes four M12 hex bolts for installation

Solid Tops are finished with paint over plated surfaces

SPECIFICATIONS

Thickness: 1.52mm
Color: Light Gray
Color Code: RAL 7035

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2T128	32643	1179mm	759mm	16mm	Mild Steel	Powder Coated
P2T168	32647	1579mm	759mm	16mm	Mild Steel	Powder Coated
P2T66HF	32658	579mm	558mm	16mm	Mild Steel	Galvanized, Powder Coated
P2T68	32663	579mm	759mm	16mm	Mild Steel	Powder Coated
P2T106	32635	979mm	558mm	16mm	Mild Steel	Powder Coated
P2T165	32645	1579mm	459mm	16mm	Mild Steel	Powder Coated
P2T86HF	32667	779mm	558mm	16mm	Mild Steel	Galvanized, Powder Coated
P2T164	32644	1579mm	358mm	16mm	Mild Steel	Powder Coated
P2T810	32664	779mm	960mm	16mm	Mild Steel	Powder Coated
P2T166	32646	1579mm	558mm	16mm	Mild Steel	Powder Coated
P2T126	32642	1179mm	558mm	16mm	Mild Steel	Powder Coated
P2T84	32665	779mm	358mm	16mm	Mild Steel	Powder Coated
P2T106HF	32634	979mm	558mm	16mm	Mild Steel	Galvanized, Powder Coated
P2T125	32638	1179mm	459mm	16mm	Mild Steel	Powder Coated
P2T85	32666	779mm	459mm	16mm	Mild Steel	Powder Coated
P2T86	32668	779mm	558mm	16mm	Mild Steel	Powder Coated
P2T124	32637	1179mm	358mm	16mm	Mild Steel	Powder Coated
P2T108	32636	979mm	759mm	16mm	Mild Steel	Powder Coated
P2T185	32648	1779mm	459mm	16mm	Mild Steel	Powder Coated
P2T45	32654	379mm	459mm	16mm	Mild Steel	Powder Coated

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2T88	32672	779mm	759mm	16mm	Mild Steel	Powder Coated
P2T188	32653	1779mm	759mm	16mm	Mild Steel	Powder Coated
P2T65	32657	579mm	459mm	16mm	Mild Steel	Powder Coated
P2T64	32656	579mm	358mm	16mm	Mild Steel	Powder Coated
P2T186	32652	1779mm	558mm	16mm	Mild Steel	Powder Coated
P2T104	32632	979mm	358mm	16mm	Mild Steel	Powder Coated
P2T46	32655	379mm	558mm	16mm	Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2T105	32633	979mm	459mm	16mm	Mild Steel	Powder Coated
P2T66	32662	579mm	558mm	16mm	Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE