

ProLine Solid Cover



Use a Solid Cover on the front or rear of the enclosure frame as a substitute for a door. Solid covers attach to the enclosure frame with semi-flush screws and include hangers for easy alignment of cover screws. They include a foam-in-place urethane gasket and two ground studs. Mounting hardware is included.

FEATURES

EMC covers are finished with paint over plated surfaces

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PCS207HF2	11809	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS146SS	31579	Stainless Steel 304	Brushed			1.52mm
PCS76HF2	11689	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS186	96430	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS76	96360	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS146HF2	11709	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS204	25439	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS76SS	31559	Stainless Steel 304	Brushed			1.52mm
PCS227	96520	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS186HF2	11759	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS184	29834	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS206	96470	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS146	96380	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS226SS	31679	Stainless Steel 304	Brushed			1.52mm
PCS206HF2	11799	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS226HF2	11839	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS186SS	31619	Stainless Steel 304	Brushed			1.52mm
PCS166	96400	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS226	96510	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS126	29832	Mild Steel		Light Gray	RAL 7035	1.52mm

Table 2/3

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PCS206SS	31649	Stainless Steel 304	Brushed			1.52mm
PCS166SS	31599	Stainless Steel 304	Brushed			1.52mm
PCS207	96480	Mild Steel		Light Gray	RAL 7035	1.52mm
PCS188	96450	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS208	96490	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS2010SS	31669	Stainless Steel 304	Brushed			1.9mm
PCS1810	96460	Mild Steel		Light Gray	RAL 7035	1.9mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PCS148	96390	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS228SS	31689	Stainless Steel 304	Brushed			1.9mm
PCS168	96420	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS208HF2	11819	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS208SS	31659	Stainless Steel 304	Brushed			1.9mm
PCS228	96530	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS148HF2	11719	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS209	29836	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS2210	96540	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS1810HF2	11789	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS148SS	31589	Stainless Steel 304	Brushed			1.9mm
PCS78SS	31569	Stainless Steel 304	Brushed			1.9mm
PCS128	29833	Mild Steel		Light Gray	RAL 7035	1.9mm

Table 3/3

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PCS78HF2	11699	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS189	29835	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS188SS	31629	Stainless Steel 304	Brushed			1.9mm
PCS78	96370	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS2010	96500	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS188HF2	11779	Mild Steel		Light Gray	RAL 7035	1.9mm
PCS2010HF2	11829	Mild Steel		Light Gray	RAL 7035	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE