

Cablecat J-hook, steel, PG, 0.75" dia

Data Solutions

CATALOG NUMBER

CAT12



CERTIFICATIONS



FEATURES

Many sizes and designs available to attach to a variety of structures

Cost effective alternative to expensive cable tray

Galvanized finish on J-Hooks provide smoother cable pull and greater corrosion resistance

cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems

PRODUCT ATTRIBUTES

Material: Steel


Finish: Pregalvanized

Diameter (Ø): 19.1mm

Height (H): 80.3mm

Cable Capacity, Cat 5e: 16

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE