

nVent CADDY Cablecat J-Hook with BC200 Beam Clamp, 3/4" dia, 1/8"–1/2" Flange

Data Solutions

CATALOG NUMBER

CAT12BC200



CERTIFICATIONS



FEATURES

Beam clamp with attached nVent CADDY Cablecat J-Hook

Supports low voltage cables

PRODUCT ATTRIBUTES


Material: Steel

Finish: Pregalvanized

Diameter (Ø): 19mm

Flange Thickness (FT): 3 – 12mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE