

# nVent CADDY Cat HP J-Hook Clip to Rod/Wire Clip, 1/2", 5/8" Rod

## Data Solutions

### CATALOG NUMBER

**CATHP8Z34**



### CERTIFICATIONS



### FEATURES

Quick attachment to threaded rod or wire

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability

Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

## PRODUCT ATTRIBUTES

---

Material: Spring Steel

Finish: nVent CADDY Armour

Rod Size (RS): 14; 18

Wire Size: 1mm min

Static Load: 220N

## ADDITIONAL PRODUCT DETAILS

---

Recommended for use with nVent CADDY Cat HP J-Hooks with a diameter of 2" (50 mm) or less.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**