

Panel 19-inch Hinged Wall-Mount 1U, Black, Steel

Data Solutions

CATALOG NUMBER

E19HPM1U



The 19-inch Hinged Panel provides a solution for smaller network equipment, punch-downs and patch panels in areas where floor space is at a premium. Easy access facilitates component installation and future expansion without disturbing existing equipment or cabling. Can be mounted with hinges on left or right side.

INDUSTRY STANDARDS

UL 2416 Listed; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

FEATURES

Open design offers unrestricted airflow

Large cable exit holes on back surface

Keyhole mounting slots on 16-in. centers accommodate up to 3/8- inch diameter mounting fasteners (not supplied)

Heavy duty hinges are welded to frame

Hinge provided for every two rack unit spacing

One rack unit model has half-size hinge

Provides access to rear of equipment

PRODUCT ATTRIBUTES

Article Number: 11001

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 2.66mm

Rack Units: 1U

Load Rating: 11.3kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE