

ProLine Containment System Window Ceiling Panel

Data Solutions



Window Ceiling Panels have easily modified, .22-inch (6 mm) polycarbonate panels to accommodate local fire-suppression codes. Overhead window panel made of .22-in. polycarbonate.

FEATURES

Frame made of 16 gauge steel

Overhead window panel made of .22-inch polycarbonate

Sealed containment, Window Ceiling Panels have easily modified .22-in. polycarbonate panels to accommodate local firesuppression codes (sprinkler heads)

Tool-less Ceiling Panels are easy to install and remove for cleaning and provide above-the-cabinet access to cables, equipment and systems

Clear, transparent door and roof panels provide maximum light to aisleway

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PCP312	38766	143mm	1309mm	297mm	Mild Steel	Powder Coated

Table 2/2

Catalog Number	Article Number	Color	Color Code	Thickness	Aisle Width
PCP312	38766	Jet Black	RAL 9005	1.52mm	1219mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE