

ProLine Window Doors for Upper Front



Window Doors fit on the upper front of the PC frame and are hinged on the left side. A 2-point latch system is operated by a Small Flush Bezel with tool-to-open insert located on the lower right side of the door. Other inserts and a Flush Swing Handle are also available.

FEATURES

Doors have .25-in.-thick clear safety glass windows

Foam-in-place gaskets for an effective seal

SPECIFICATIONS

Thickness: 1.9mm
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Window Size	Fits PC Frame
PDWTL96PC	30869	Mild Steel	436 x 451mm	1800 x 600mm
PDWT86PC	98340	Mild Steel	343 x 366mm	1600 x 600mm
PDWTL86PC	30859	Mild Steel	436 x 451mm	1600 x 600mm
PDWT108PC	98390	Mild Steel	343 x 566mm	2000 x 800mm
PDWT106PC	98380	Mild Steel	343 x 366mm	2000 x 600mm
PDWT96PC	98360	Mild Steel	343 x 366mm	1800 x 600mm
PDWT98PC	98370	Mild Steel	343 x 566mm	1800 x 800mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE