

Rack Angles



Rack Angles are used to install 19-in. wide equipment in 25.5-in. wide enclosures and 23-in. wide equipment in 36-in. wide enclosures. Order two sets for 52- and 72-in. wide two-door enclosures. Rack Angles have square holes spaced to meet EIA 310-D standards. Mount to factory-drilled holes in top and bottom of front flange. Purchase clip nuts, catalog number AN1032, separately for component mounting.

FEATURES

Used to install standard rack mounted equipment in enclosures that have back panel mounting provisions

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Thickness
ARA4819THG	13808	Mild Steel	Galvanized	1.9mm
ARA6019THG	13811	Mild Steel	Galvanized	1.9mm
ARA7219THG	13812	Mild Steel	Galvanized	1.9mm
ARA8419THG	13813	Mild Steel	Galvanized	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE