

## Section Profiles For Cable Entry, SCE



This click-in section profile has a pre-mounted gasket to seal the empty space around cables routed between bottom plates, which maintains the enclosure's protection degree.

### FEATURES

---

Description: For sealing the cable entry between gland plates. Forms a tight seal around cables and fills gaps to prevent dust from entering. The foam is pre-fitted in the section profile that can be easily mounted in the bottom plates thanks to its click-in fixing solution. An alternative to the bottom late gasket kit BG01.

Material: Extruded PVC section profile. Gasket: adhesive foam with cross-section of 30 x 25 mm.

Pack quantity: 1 set consisting of 2 click-in section profiles with foam rubber. SCE-R variant includes an extra bottom plate.

## SPECIFICATIONS

**Thickness:** 1.2mm  
**Color:** Black  
**Material:** PVC  
**Finish:** Smooth Matte

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Enclosure Material	For Mounting
SCE1200R		30mm	1200mm	20mm	PVC	In Rearmost Position
SCE600	SCE600	30mm	600mm	20mm	PVC	In Depth
SCE1000	SCE1000	30mm	1000mm	20mm	PVC	In Depth
SCE800	SCE800	30mm	800mm	20mm	PVC	In Depth
SCE800R		30mm	800mm	20mm	PVC	In Rearmost Position
SCE1000R		30mm	1000mm	20mm	PVC	In Rearmost Position
SCE1200	SCE1200	30mm	1200mm	20mm	PVC	In Depth
SCE600R		30mm	600mm	20mm	PVC	In Rearmost Position

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**