

Rack-Mount Adjustable Shelf

Data Solutions



The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles. The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement. There are both solid and vented models available. They fit 19- or 23-inch rack spacing and require only 1U of rack space. Please note the load rating is for 150 lb. (68 kg).

FEATURES

The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles

The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement

There are both solid and vented models available

They fit 19- or 23-inch rack spacing and require only 1U of rack space

Please note the load rating is for 150 lb. (68 kg)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
P19SH810	47409	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.9mm
P23SH810B	12956	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
P19SH810B	47919	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
P19SH68	47399	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.9mm
P19VSH68B	11053	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
P19SH68B	47909	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
P23SH68B	12955	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
P23VSH810B	11056	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
P23VSH68B	11055	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm
P19VSH810B	11054	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.9mm

Table 2/2

Catalog Number	Article Number	Type	Length	Width	Max Depth	Fits Enclosure Depth
P19SH810	47409	Solid	700mm	439mm	980mm	1000mm max
P23SH810B	12956	Solid	700mm	541mm	980mm	1000mm max
P19SH810B	47919	Solid	700mm	439mm	980mm	1000mm max
P19SH68	47399	Solid	500mm	439mm	780mm	800mm max
P19VSH68B	11053	Vented	500mm	439mm	780mm	800mm max
P19SH68B	47909	Solid	500mm	439mm	780mm	800mm max
P23SH68B	12955	Solid	500mm	541mm	780mm	800mm max
P23VSH810B	11056	Vented	700mm	541mm	980mm	1000mm max
P23VSH68B	11055	Vented	500mm	541mm	780mm	800mm max
P19VSH810B	11054	Vented	700mm	439mm	980mm	1000mm max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE