

ProLine Solid Door



Solid Doors include a removable door bar system on doors taller than 700 mm and wider than 400 mm. Hinge side is reversible. A flush bezel latch operates the 3-point latching system. Doors for 700-mm frames have 2-point latching. Hidden hinges (130-degree swing) permit attachment to the front or back of each enclosure frame. The use of a side-door adapter or a cable entry cabinet allows doors to be attached to the sides of the enclosure frame.

FEATURES

EMC doors are finished with paint over plated surfaces

Optional data pockets, door stops, grounding kits and 180-degree hinges are available

Hinges have easy slide retained hinge pins

Door gasket is foam-in-place urethane to provide a resilient, seamless seal

Two grounding studs are furnished. All mounting hardware is included

SPECIFICATIONS

Color: Light Gray

Color Code: RAL 7035

Table 1/2

Catalog Number	Article Number	Material	Thickness	Dimensions	Fits Frame	Door Type
PDS206HF2	13579	Mild Steel	1.52mm	1939 x 592mm	2000 x 600mm	EMC
PDS76R	94840	Mild Steel	1.52mm	639 x 592mm	700 x 600mm	Steel
PDS165	35019	Mild Steel	1.52mm	1539 x 492mm	1600 x 500mm	Steel
PDS146HF2	13489	Mild Steel	1.52mm	1339 x 592mm	1400 x 600mm	EMC
PDS204	25429	Mild Steel	1.52mm	1939 x 392mm	2000 x 400mm	Steel
PDS186HF2	13539	Mild Steel	1.52mm	1739 x 592mm	1800 x 600mm	EMC
PDS207HF2	13589	Mild Steel	1.52mm	1939 x 692mm	2000 x 700mm	EMC
PDS166	94880	Mild Steel	1.52mm	1539 x 592mm	1600 x 600mm	Steel
PDS146	94860	Mild Steel	1.52mm	1339 x 592mm	1400 x 600mm	Steel
PDS186	94910	Mild Steel	1.52mm	1739 x 592mm	1800 x 600mm	Steel
PDS227HF2	13629	Mild Steel	1.52mm	2139 x 692mm	2200 x 700mm	EMC
PDS205	35039	Mild Steel	1.52mm	1939 x 492mm	2000 x 500mm	Steel
PDS207	94960	Mild Steel	1.52mm	1939 x 692mm	2000 x 700mm	Steel
PDS225	35049	Mild Steel	1.52mm	2139 x 492mm	2200 x 500mm	Steel
PDS185	35029	Mild Steel	1.52mm	1739 x 492mm	1800 x 500mm	Steel
PDS227	95000	Mild Steel	1.52mm	2139 x 692mm	2200 x 700mm	Steel
PDS206	94950	Mild Steel	1.52mm	1939 x 592mm	2000 x 600mm	Steel
PDS184	29824	Mild Steel	1.52mm	1739 x 392mm	1800 x 400mm	Steel
PDS226	94990	Mild Steel	1.52mm	2139 x 592mm	2200 x 600mm	Steel
PDS126	29822	Mild Steel	1.52mm	1139 x 592mm	1200 x 600mm	Steel

Table 2/2

Catalog Number	Article Number	Material	Thickness	Dimensions	Fits Frame	Door Type
PDS188HF2	13559	Mild Steel	1.9mm	1739 x 792mm	1800 x 800mm	EMC
PDS128	29823	Mild Steel	1.9mm	1139 x 792mm	1200 x 800mm	Steel
PDS2010	94980	Mild Steel	1.9mm	1939 x 992mm	2000 x 1000mm	Steel
PDS148HF2	13499	Mild Steel	1.9mm	1339 x 792mm	1400 x 800mm	EMC
PDS208	94970	Mild Steel	1.9mm	1939 x 792mm	2000 x 800mm	Steel
PDS148	94870	Mild Steel	1.9mm	1339 x 792mm	1400 x 800mm	Steel
PDS208HF2	13599	Mild Steel	1.9mm	1939 x 792mm	2000 x 800mm	EMC
PDS228	95010	Mild Steel	1.9mm	2139 x 792mm	2200 x 800mm	Steel
PDS2010HF2	13609	Mild Steel	1.9mm	1939 x 992mm	2000 x 1000mm	EMC
PDS1810HF2	13569	Mild Steel	1.9mm	1739 x 992mm	1800 x 1000mm	EMC

Catalog Number	Article Number	Material	Thickness	Dimensions	Fits Frame	Door Type
PDS188	94930	Mild Steel	1.9mm	1739 x 792mm	1800 x 800mm	Steel
PDS78R	94850	Mild Steel	1.9mm	639 x 792mm	700 x 800mm	Steel
PDS1810	94940	Mild Steel	1.9mm	1739 x 992mm	1800 x 1000mm	Steel
PDS2210	95020	Mild Steel	1.9mm	2139 x 992mm	2200 x 1000mm	Steel
PDS78RHF2	13479	Mild Steel	1.9mm	639 x 792mm	700 x 800mm	EMC
PDS168	94900	Mild Steel	1.9mm	1539 x 792mm	1600 x 800mm	Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE