

MultipacPRO Mounting Plate



Mounting plates are designed for the mounting of heavy components, e.g. transformers.

CERTIFICATIONS



FEATURES

Mounting plates are designed for the mounting of heavy components, e.g. transformers

Bolted laterally inside on a 19" chassis

SPECIFICATIONS

- Material:** Aluminum
- Works With:** Chassis
- Product Type:** Mounting Plate
- Product Family:** MultipacPRO

Table 1/1

Catalog Number	Depth	Package Quantity	Rack Width	Width	Certifications
20860-107	150mm	1	84HP	402.5mm	RoHS
20860-112	450mm	1	84HP	402.5mm	
20860-111	390mm	1	84HP	402.5mm	RoHS
20860-108	210mm	1	84HP	402.5mm	RoHS
20860-110	330mm	1	84HP	402.5mm	RoHS
20860-109	270mm	1	84HP	402.5mm	RoHS

ADDITIONAL PRODUCT DETAILS

Mounting plates can also be fitted at the same time as the internal mounting for euroboards.

Where a mounting plate is used the clear mounting height is reduced by at least 2.5 mm.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE