

CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



CERTIFICATIONS



FEATURES

The front panel is bolted to the front frame of the enclosure

SPECIFICATIONS

- Material:** Aluminum
- Finish:** Anodized
- Accessory Type:** Front panel
- Product Type:** Front Panel

Table 1/2

| Catalog Number | Rack Height | Rack Width | Depth | Package Quantity | Front Finish | Rear Finish |
|----------------|-------------|------------|-------|------------------|--------------|-------------|
| 30823-227 | 4U | 63HP | 3mm | 1 | Anodized | Anodized |
| 30823-209 | 2U | 42HP | 3mm | 1 | Anodized | Anodized |
| 30823-224 | 3U | 63HP | 3mm | 1 | Anodized | Anodized |
| 30823-284 | 6U | 84HP | 3mm | 1 | Anodized | Anodized |
| 30823-254 | 3U | 28HP | 3mm | 1 | Anodized | Anodized |
| 30823-272 | 4U | 84HP | 3mm | 1 | Anodized | Anodized |

| Catalog Number | Rack Height | Rack Width | Depth | Package Quantity | Front Finish | Rear Finish |
|----------------|-------------|------------|-------|------------------|--------------|-------------|
| 30823-269 | 4U | 42HP | 3mm | 1 | Anodized | Anodized |
| 30823-257 | 3U | 42HP | 3mm | 1 | Anodized | Anodized |
| 30823-260 | 3U | 84HP | 3mm | 1 | Anodized | Anodized |
| 30823-215 | 2U | 84HP | 3mm | 1 | Anodized | Anodized |
| 30823-230 | 6U | 63HP | 3mm | 1 | Anodized | Anodized |

Table 2/2

| Catalog Number | Treated Edges | EMC Shielding | Height | Width |
|----------------|---------------|---------------|---------|---------|
| 30823-227 | No | No | 172.9mm | 345.4mm |
| 30823-209 | No | No | 84mm | 238.7mm |
| 30823-224 | No | No | 128.4mm | 345.4mm |
| 30823-284 | No | No | 261.8mm | 452.1mm |
| 30823-254 | No | No | 128.4mm | 167.5mm |
| 30823-272 | No | No | 172.9mm | 452.1mm |
| 30823-269 | No | No | 172.9mm | 238.7mm |
| 30823-257 | No | No | 128.4mm | 238.7mm |
| 30823-260 | No | No | 128.4mm | 452.1mm |
| 30823-215 | No | No | 84mm | 452.1mm |
| 30823-230 | No | No | 261.8mm | 345.4mm |

ADDITIONAL PRODUCT DETAILS

Assembly Kit to fix one rear and one front panel is included with the case.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE