

MI PDU, 1U, 16A, 230V, 1P, (9)C13/C15/C19/C21

Data Solutions

CATALOG NUMBER

EN1361

The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

UL 2900-1 certified for safety software cybersecurity for network-connectable products.

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs

Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

PRODUCT ATTRIBUTES

Product Family: Enlogic
Type: Intelligent PDU
Product Type: Socket Strip
Socket Type: (9) C13/C15/C19/C21
Socket Quantity: 9
Color: Black
Switched Outlets: No
Cable Length: 3000mm
Power Rating: 3.7 kVA
Circuit Breaker: No Circuit Breaker
Circuit Breaker Quantity: 0
Phase: 1 PH
Nominal Power Output: 230VAC
Nominal Voltage: 230V
Number of Output Voltages: 12
On/Off Switch Included: No
Output Voltage: 230VAC
Amperage (Derated Amperage): 16 A
Plug Type: IEC 60309 316P6 (IP44)
Rack Units: 1U
Removable Input Cable: Yes
Metering Type: Input
Material: Steel
Finish: Powder Coated
Height: 43mm
Width: 444mm
Depth: 269mm
Weight: 4.4kg
Package Quantity: 1
Input Cable Length: 3m

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE