

# Outdoor Modular 29 U 1530H 900W 700D

## Data Solutions

### CATALOG NUMBER

**10149-645**



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

### FEATURES

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from front, all sides possible upon request

100 mm high plinth, 200 and 300 mm possible

Top cover with louvers, can be upgraded with fans or A/C unit

RAL 7035 powder coating, other colors available upon request

### PRODUCT ATTRIBUTES

Product Type: Outdoor Cabinet

Product Family: Modular

Rack Height: 29U

Height: 1530mm

Width: 900mm

Depth: 700mm

Wall Type: Double Walled

Door Type: Plain; Double Door

Cooling: Passive

EMC Shielding: Optional

Package Quantity: 1

Battery Compartment: Optional

Burglar Resistance: Optional

Finish: Powder Coated

Frame Material: Aluminum

Material: Aluminum; Steel

Plinth Height: 100mm

Mounting Setup: Optional

## ADDITIONAL PRODUCT DETAILS

---

Height dimensions are without base/plinth.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**