We connect and protect

Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 250 kcmil Ropelay, Left Hand

Data Solutions

CATALOG NUMBER

PBWT202WLH

FEATURES

- Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis
- Includes mold cleaner and flint ignitor

PRODUCT ATTRIBUTES

- Material: Graphite; Steel; Thermoplastic
- Rail Type: 85 lb to 141 lb T-Rail Sections
- Bond Terminal Style: W
- Conductor Size: 250 kcmil Ropelay
- Conductor Outer Diameter, Nominal: 19.05mm
- Welder Style: T20
- Orientation: Left Hand
- Mold Only: No
- Replacement Mold: PBW2W
- Welding Material: PB115, Sold Separately
- Handle Clamp: C105C, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.