


# LHX+ In-Rack Cooler, Air/Liquid Heat Exchanger, Fixed Speed, 10 KW, 115 V, 2 Fans, 6 U, 550D

## Data Solutions

### CATALOG NUMBER

**29714-033**



### FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

UL Certified

### PRODUCT ATTRIBUTES

Fan Quantity: 2

Input Voltage AC: 100 – 115V

Package Quantity: 1

Supply Voltage: 115V min

Redundant Power Supply: No

Coolant Feed: Bottom

Airflow Direction: Front to Top

Depth: 500mm

Height: 266mm

Product Family: Cooling

Product Type: Air/Liquid Heat Exchanger

Width: 426mm

Works With: Varistar; Varistar CP

## ADDITIONAL PRODUCT DETAILS

---

Please order separately: Monitoring via Control unit, water control package, display and door contact switch.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**