

# ProLine ConneCTek Communications Patch Cabinet

## Data Solutions



The ProLine ConneCTek Network Communication/Patch Cabinets feature two vertical cable managers in the front of the cabinet and two rear cable managers for maximum cable routing and support. Cabinets are available in two widths to accommodate high-density cables, patch cords and networking equipment.

### FEATURES

Aesthetically pleasing front door offers optimal airflow and durability

Fully perforated top, front door and rear doors allow maximum air movement around cables, patch panels and other network equipment

Front and rear open cable managers provide ability to support and route cable

Side-less models allow for easy installation in ganging applications

Common profiles allow ganging of server and networking cabinets

Top gland plate allows easy routing of cable, pre-terminated cables and patch panels

Three-point locking swing handle allows for easy but controlled access; two keys included

### SPECIFICATIONS

- Color:** Jet Black
- Material:** Mild Steel
- Finish:** Powder Coated
- Color Code:** RAL 9005

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
----------------	----------------	--------	-------	-------	-----------	------------

PNC24810B	26393	2411mm	806mm	999mm	1.52mm	51U
PNC20711B	15615	1991mm	707mm	1099mm	1.52mm	42U
PNC24811B	26394	2411mm	806mm	1099mm	1.52mm	51U
PNC20811BNS	16073	1991mm	799mm	1099mm	1.52mm	42U
PNC21812B	26391	2161mm	806mm	1199mm	1.52mm	45U
PNC2089BNS	16071	1991mm	799mm	899mm	1.52mm	42U
PNC21811B	26388	2161mm	806mm	1099mm	1.52mm	45U
PNC2079B	15613	1991mm	707mm	899mm	1.52mm	42U
PNC20711BNS	15621	1991mm	699mm	1099mm	1.52mm	42U
PNC20710BNS	15618	1991mm	699mm	999mm	1.52mm	42U
PNC20811B	16067	1991mm	808mm	1099mm	1.52mm	42U
PNC24812B	26395	2411mm	806mm	1199mm	1.52mm	51U
PNC2089B	16065	1991mm	808mm	874mm	1.52mm	42U
PNC20812B	16068	1991mm	808mm	1199mm	1.52mm	42U
PNC20810B	16066	1991mm	808mm	999mm	1.52mm	42U
PNC20812BNS	16074	1991mm	799mm	1199mm	1.52mm	42U
PNC20712BNS	15622	1991mm	699mm	1199mm	1.52mm	42U
PNC2079BNS	15617	1991mm	699mm	899mm	1.52mm	42U
PNC20710B	15614	1991mm	707mm	999mm	1.52mm	42U
PNC20810BNS	16072	1991mm	799mm	999mm	1.52mm	42U

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
PNC2189B	26386	2161mm	806mm	899mm	1.52mm	45U
PNC20712B	15616	1991mm	707mm	1199mm	1.52mm	42U
PNC21810B	26387	2161mm	806mm	999mm	1.52mm	45U
PNC2489B	26392	2411mm	806mm	899mm	1.52mm	51U

Table 1/2

Catalog Number	Article Number	Side Covers Included
PNC24810B	26393	Yes
PNC20711B	15615	Yes
PNC24811B	26394	Yes
PNC20811BNS	16073	No
PNC21812B	26391	Yes
PNC2089BNS	16071	No

Catalog Number	Article Number	Side Covers Included
PNC21811B	26388	Yes
PNC2079B	15613	Yes
PNC20711BNS	15621	No
PNC20710BNS	15618	No
PNC20811B	16067	Yes
PNC24812B	26395	Yes
PNC2089B	16065	Yes
PNC20812B	16068	Yes
PNC20810B	16066	Yes
PNC20812BNS	16074	No
PNC20712BNS	15622	No
PNC2079BNS	15617	No
PNC20710B	15614	Yes
PNC20810BNS	16072	No

Table 2/2

Catalog Number	Article Number	Side Covers Included
PNC2189B	26386	Yes
PNC20712B	15616	Yes
PNC21810B	26387	Yes
PNC2489B	26392	Yes

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**