

VersaRack Wall-Mount Open Frame Rack

Data Solutions



VersaRack Wall-Mount Open Frame Rack is used for wall mounting and securing 19-inch rack equipment for Telecommunication Rooms and other locations. The rack provides for either left or right hinging to accommodate a variety of applications. These open frame racks are ideal for high-density cabling application. VersaRack is ideal for IDFs (Intermediate Distribution Frames), remote 19-inch rack equipment, building automation, security and many other applications.

INDUSTRY STANDARDS

UL 2416 Listed; File Number E230874

Rated to 100 lbs. with a 4X safety factor

EIA 310-D

FEATURES

Designed to accommodate all standard 19-inch rack equipment

Easy, single-tool assembly reduces installation time and cost

Spring-load pivot pins provide for either left or right hinging; pins can be arranged in unlocked or locked position

Preassembled for fast, time-saving installation

Temporary mounting bracket allows for rapid, single-person wall installation

UL double lug ground holes provide easy adherence to local bonding and grounding codes

Cable tie down points, sized for up to 1-inch Velcro® straps, provided in horizontal and vertical positions in multiple locations

Standard 12- or 24-inch deep offering to accommodate various applications

Open design provides for maximum access to cables and equipment

Smart packaging with hand-carrying holes allows for easy transportation

SPECIFICATIONS

Color:	Jet Black
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 9005

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Thickness	Load Rating
E19SWM20U24	26165	1062mm	531mm	617mm	2.66mm	45kg
E19SWM25U24	26167	1285mm	531mm	617mm	2.66mm	45kg
E19SWM12U24	26163	706mm	531mm	617mm	2.66mm	45kg
E19SWM12U12	26162	706mm	531mm	312mm	2.66mm	45kg
E19SWM20U12	26164	1062mm	531mm	312mm	2.66mm	45kg
E19SWM25U12	26166	1285mm	531mm	312mm	2.66mm	45kg

Table 2/2

Catalog Number	Article Number	Rack Units
E19SWM20U24	26165	20U
E19SWM25U24	26167	25U
E19SWM12U24	26163	12U
E19SWM12U12	26162	12U
E19SWM20U12	26164	20U
E19SWM25U12	26166	25U

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE