

Four Pole Distrib. Block with Threaded Bars, 125 A

Data Solutions

CATALOG NUMBER

TR-125A



CERTIFICATIONS



FEATURES

Easily clips onto DIN rail or mounts to panel with screws

Equipped with a current input plug

Bolts included for output connections

Transparent protection cover

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

PRODUCT ATTRIBUTES

Article Number: 563150

Material: Copper; Glass Fibre Reinforced Polyamide; Plexiglass

Max Working Voltage, IEC (Ui): 1000

Peak Short Circuit Current (Ipk): 40kA

Short Term Withstand Current (Icw) 1s: 8.4kA

Line Side Number of Connections: 1

Load Side Number of Connections: 5

Thread Size 1 (TS1): M5

Thread Size 2 (TS2): M6

Depth (D): 117mm

Height (H): 126mm

Width (W): 150mm

Unit Weight: 0.68kg

Flammability Rating: UL® 94V-0

Complies With: IEC® 60439.1; IEC® 61439.1; IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Thread Size 2 represents input plug.

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE