

DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



FEATURES

Axial 119 mm DC fan, with plug for connection cable

SPECIFICATIONS

Table 1/2

| Catalog Number | Works With | Width | Length | Height | Voltage DC | Airflow |
|----------------|---------------|-------|--------|--------|------------|----------------------|
| 60713-600 | 19" Fan Trays | 119mm | 119mm | 32mm | 12V | 140m ³ /h |
| 20713-242 | 19" Fan Trays | 119mm | 119mm | 38mm | 48V | 184m ³ /h |
| 20713-241 | 19" Fan Trays | 119mm | 119mm | 38mm | 12V | 184m ³ /h |
| 20713-240 | 19" Fan Trays | 119mm | 119mm | 38mm | 24V | 184m ³ /h |
| 20713-172 | 19" Fan Trays | 119mm | 119mm | 25.5mm | 24V | 171m ³ /h |

Table 2/2

| Catalog Number | Noise Level | Power | Max Static Pressure | Ambient Temperature | Package Quantity |
|----------------|-------------|-------|---------------------|---------------------|------------------|
| 60713-600 | 39dB(A) | 8W | 46Pa | 70°C | 1 |
| 20713-242 | 42dB(A) | 8W | 68Pa | 70°C | 1 |

| Catalog Number | Noise Level | Power | Max Static Pressure | Ambient Temperature | Package Quantity |
|----------------|-------------|-------|---------------------|---------------------|------------------|
| 20713-241 | 42dB(A) | 8W | 68Pa | 70°C | 1 |
| 20713-240 | 42dB(A) | 8W | 68Pa | 70°C | 1 |
| 20713-172 | 50.5dB(A) | 7W | 50.5Pa | 70°C | 1 |

ADDITIONAL PRODUCT DETAILS

Please order connection cable and protective grille separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE