

Crimping Compression Tool, Foot Pump

Data Solutions



FEATURES

Wide cross section range

High-pressure 2 meter (6.5') long hose

Compact and easy to use

Includes easy-to-carry custom case

SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Applied Force | System | Dies | Crimping Shape | Conductor Size |
|----------------|----------------|---------------|---------------------|-------------|----------------|--------------------------------------------------------------------------------------------------|
| M4FP | 716925 | 250kN | Foot pump hydraulic | PKM4 series | Hexagon | #6 Stranded - 1000 kcmil Stranded, 16 mm ² Stranded - 625 mm ² Stranded |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE