

19" Front Panel, Vented

Vented front panels allows heat dissipation through holes.



CERTIFICATIONS



FEATURES

Vented front panels (Aluminum) allows heat dissipation

SPECIFICATIONS

- Rack Width:** 95HP
- Material:** Aluminum
- Accessory Type:** Front panel
- Product Type:** Front Panel

Table 1/2

| Catalog Number | Rack Height | Finish | Mounting | Package Quantity | Front Finish | Rear Finish |
|----------------|-------------|---------------|----------------|------------------|--------------|-------------|
| 30118-962 | 1U | Powder Coated | Screw-on Front | 1 | Painted | Painted |
| 30702-047 | 1U | Anodized | Screw-on Front | 1 | Anodized | Anodized |
| 30702-056 | 1U | Powder Coated | Screw-on Front | 1 | Painted | Painted |
| 30702-044 | 1U | Anodized | Screw-on Front | 1 | Raw | Conductive |
| 30118-963 | 2U | Anodized | Screw-on Front | 1 | Painted | Painted |
| 30702-048 | 2U | Anodized | Screw-on Front | 1 | Anodized | Anodized |

| Catalog Number | Rack Height | Finish | Mounting | Package Quantity | Front Finish | Rear Finish |
|----------------|-------------|---------------|----------------|------------------|--------------|-------------|
| 30702-057 | 2U | Powder Coated | Screw-on Front | 1 | Painted | Painted |
| 30118-964 | 3U | Powder Coated | Screw-on Front | 1 | Painted | Painted |
| 30702-058 | 3U | Powder Coated | Screw-on Front | 1 | Painted | Painted |
| 30702-046 | 3U | Anodized | Screw-on Front | 1 | Raw | Raw |
| 30702-045 | 2U | Anodized | Screw-on Front | 1 | Raw | Raw |
| 30702-049 | 3U | Anodized | Screw-on Front | 1 | Anodized | Anodized |

Table 2/2

| Catalog Number | Treated Edges | Color Code | EMC Shielding | Height (H) | Type | Width (W) |
|----------------|---------------|------------|---------------|------------|-----------------|-----------|
| 30118-962 | | RAL 7021 | No | 43.6mm | 19" Front Panel | 483mm |
| 30702-047 | Yes | | No | 43.6mm | 19" Front Panel | 483mm |
| 30702-056 | | RAL 7035 | No | 43.6mm | 19" Front Panel | 483mm |
| 30702-044 | | | No | 43.6mm | 19" Front Panel | 483mm |
| 30118-963 | | RAL 7021 | No | 88.1mm | 19" Front Panel | 483mm |
| 30702-048 | Yes | | No | 88.1mm | 19" Front Panel | 483mm |
| 30702-057 | | RAL 7035 | No | 88.1mm | 19" Front Panel | 483mm |
| 30118-964 | | RAL 7021 | No | 132.5mm | 19" Front Panel | 483mm |
| 30702-058 | | RAL 7035 | No | 132.5mm | 19" Front Panel | 483mm |
| 30702-046 | | | No | 132.5mm | 19" Front Panel | 483mm |
| 30702-045 | | | No | 88.1mm | 19" Front Panel | 483mm |
| 30702-049 | Yes | | No | 132.5mm | 19" Front Panel | 483mm |

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE