

# Connection clamp with levers

Distribution Clamps for Distribution Box.



## FEATURES

Connection clamp with levers

For all conductor types

3 or 5 conductors

Up to 4.00 mm<sup>2</sup>

## SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Color	Ambient Temperature	Clamp Quantity	Depth	Height
20118-902	Clamp	Transparent, Green	85°C max	3	18.8mm	8.4mm
20118-903	Clamp	Transparent, Green	85°C max	5	18.8mm	8.4mm

Table 2/2

Catalog Number	Material	Max Current	Max Voltage	Package Quantity	Weight	Width
20118-902	Polycarbonate	20A	600V	10	2.5g	18.8mm
20118-903	Polycarbonate	20A	600V	10	4g	30mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte**