

# KN Hook



## FEATURES

Use to repair a link or combine two chains together by hammering the link shut

## SPECIFICATIONS


**Finish:** Electrogalvanized

**Material:** Steel

Table 1/1

Catalog Number	Article Number	Diameter (Ø)	Length (L)	B	Static Load
KN30EG	380050	3 mm	16.5mm	12.5 mm	370N
KN40EG	380060	4 mm	20mm	16 mm	550N
KN50EG	380070	5 mm	23mm	20 mm	950N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

